



GB148 Shown

### Standard Colors:



Velvet Red  
(Installed)



Coastal Blue  
(Included in Box)

### NEW Sporty Optional Colors:



Crisp White



Canary Yellow



Stone Grey



Orchid Pink



Army Green  
(Matte)



Desert Tan



### Sporty New LED Running Light on the 4-W EX!

## Buzzaround 3-wheel GB118 4-wheel GB148



The Golden Buzzaround Extreme Scooter features the portability and easy disassembly of a lightweight scooter with the amazing benefits of a full-size scooter! Standard comfort features on the Buzzaround EX include a stylish quilted high back seat, an infinite adjustable tiller at your fingertips, and a USB charging port right under the dashboard. The 4-Wheel model features a sporty new LED V-shaped running light on the front for maximum safety and visibility. The Buzzaround EX also comes standard with 2-U1 batteries - industry leading and the largest battery in this category - for maximum operating range up to 18 miles. With a 350 lb. weight capacity, comfort spring suspension, and 40.5" turning radius, the Buzzaround EX offers a smooth ride. Go the extra mile on a BuzzAround Extreme Scooter!



### Standard Features:

- 350 lb. weight capacity
- 4" ground clearance
- Full size & portable
- Larger 90 amp controller
- Larger 320 watt motor
- Larger 9" tires
- U1 battery for maximum range
- Ultrabright LED headlight & tail light
- Comfort suspension springs
- Full size, yet portable & easy to disassemble



| Model                              | GB118                   | GB148                   |
|------------------------------------|-------------------------|-------------------------|
| Description                        | EX                      | EX                      |
| Medicare Code                      | Not Coded               | Not Coded               |
| Weight Capacity                    | 350 lbs.                | 350 lbs.                |
| Drive Wheels                       | Rear                    | Rear                    |
| Maximum Speed                      | 5 mph                   | 5 mph                   |
| Operating Range up to <sup>1</sup> | 18 miles                | 18 miles                |
| Under Deck Clearance               | 4"                      | 4"                      |
| Turning Radius                     | 40.5"                   | 54"                     |
| Type Batteries                     | 2-U1                    | 2-U1                    |
| Colors                             | Red, Blue               | Red, Blue               |
| Freewheel Mode                     | Yes                     | Yes                     |
| Electronic Speed Control           | Yes                     | Yes                     |
| Electro-Mechanical Brakes          | Yes                     | Yes                     |
| Charger                            | Off-board               | Off-board               |
| Controller                         | 90 Amp Dynamic R-Series | 90 Amp Dynamic R-Series |

**Dimensions:**

|                                        |               |               |
|----------------------------------------|---------------|---------------|
| Length                                 | 45"           | 44"           |
| Width                                  | 22"           | 22"           |
| Height (ground to top of back of seat) | 35"-37"       | 35"-37"       |
| Ground to Top of Seat                  | 22.75"-24.75" | 22.75"-24.75" |
| Ground to Top of Deck                  | 6.75"         | 6.75"         |
| Deck to Top of Seat                    | 16"-18"       | 16"-18"       |
| Number of Seat Height Positions        | 3             | 3             |
| Size of Increments                     | 1"            | 1"            |
| Front Axle to Rear Axle                | 34.7"         | 33.8"         |

**Weight of Unit: (assembled)**

|             |                  |                  |
|-------------|------------------|------------------|
| Front Half  | 154 lbs.         | 161 lbs.         |
| Rear Half   | 46 lbs.          | 53 lbs.          |
| Seat w/Arms | 36 lbs.          | 36 lbs.          |
| Batteries   | 23 lbs.          | 23 lbs.          |
|             | 24 lbs. per pack | 24 lbs. per pack |

**Tires:**

|                      |                    |                    |
|----------------------|--------------------|--------------------|
| Standard Tires       | Solid, low profile | Solid, low profile |
| Optional Tires       | N/A                | N/A                |
| Front                | 9"                 | 9"                 |
| Rear                 | 9"                 | 9"                 |
| Rear Anti-Tip Wheels | 2"                 | 2"                 |

**Standard Seat** Highback Highback

|                                |             |             |
|--------------------------------|-------------|-------------|
| Seat Back Height - no headrest | 18"         | 18"         |
| Width x Depth                  | 18" x 16"   | 18" x 16"   |
| Color                          | Black Vinyl | Black Vinyl |

**Optional Seat:** Stadium Style Stadium Style

|                           |             |             |
|---------------------------|-------------|-------------|
| Back Height - no headrest | 16"         | 16"         |
| Width x Depth             | 20"x 18"    | 20"x 18"    |
| Color                     | Black Vinyl | Black Vinyl |

**Warranty:**

|                          |                   |                   |
|--------------------------|-------------------|-------------------|
| Frame                    | Lifetime Warranty | Lifetime Warranty |
| Drive Train              | 2 Year Warranty   | 2 Year Warranty   |
| Electronics <sup>2</sup> | 2 Year Warranty   | 2 Year Warranty   |
| Batteries                | 1 Year Warranty   | 1 Year Warranty   |

<sup>1</sup> Battery range at 200 lbs. and will vary due to rider weight, drive surface, terrain, and battery type.

<sup>2</sup> Electronics warranty excludes batteries.

FDA Class II Medical Devices designed by Golden Technologies are intended to assist persons with chronic physical disabilities.

## Wireless disassembly in 4 easy steps!



Step 1: Pop off the seat!



Step 2: Pull out the battery pack!



Step 3: Fold down tiller and lock in place!



Step 4: Pull forward on the drivetrain release lever to separate the front and rear frame sections!



Disassembles into 6 pieces!

4 wheel model shown



A battery charging port is conveniently located on the tiller under the control panel.



Phone: 800-624-6374

Fax: 800-628-5165

www.goldentech.com



www.facebook.com/goldentechnologies